

Custom Ptfе Bottles For Diverse Industrial Applications

Item Number: PL-1010



Introduction

High-purity PTFE bottles for chemical storage, resistant to acids & solvents. Wide/narrow mouth options, leak-proof, durable. Ideal for labs & industry.

[Learn More](#)

Volume	Height	Diameter	Mouth Diameter	Weight
50ml	86mm	45mm	22mm	94.4g
100ml	107mm	54mm	30mm	144.7g
150ml	110mm	62mm	30mm	183.3g
200ml	123mm	70mm	37mm	244.9g
250ml	131mm	71mm	37mm	248g
500ml	153mm	82mm	35mm	364.7g
1000ml	195mm	109mm	51mm	836.2g

Volume	Height	Diameter	Mouth Diameter	Weight
50ml	86mm	45mm	22mm	94.4g
100ml	115mm	54mm	22mm	133.9g
150ml	110mm	62mm	22mm	173.8g
200ml	126mm	70mm	30mm	228g
250ml	135mm	71mm	30mm	242g
500ml	154mm	82mm	30mm	340.7g
1000ml	190mm	109mm	35mm	733.6g