

Custom Ptfе Sealing Tapes For Industrial And High Tech Applications

Item Number: PL-05



Introduction

KINTEK's PTFE sealing tape offers superior leak protection, chemical resistance, and high-temperature performance for industrial applications. Custom sizes available.

[Learn More](#)

Dimensions (Width x Thickness)	Approx. Length per Roll	Dimensions (Width x Thickness)	Approx. Length per Roll
6 mm x 3 mm	~335 m	20 mm x 3 mm	~100 m
6 mm x 5 mm	~192 m	20 mm x 4 mm	~74 m
8 mm x 3 mm	~251 m	20 mm x 5 mm	~57 m
8 mm x 5 mm	~144 m	25 mm x 3 mm	~80 m
10 mm x 3 mm	~201 m	25 mm x 5 mm	~46 m
10 mm x 4 mm	~147 m	30 mm x 3 mm	~67 m
10 mm x 5 mm	~115 m	30 mm x 4 mm	~49 m
12 mm x 3 mm	~167 m	30 mm x 5 mm	~38 m
12 mm x 5 mm	~96 m	40 mm x 3 mm	~50 m
15 mm x 3 mm	~134 m	40 mm x 5 mm	~29 m
15 mm x 5 mm	~77 m	50 mm x 3 mm	~40 m
		50 mm x 5 mm	~23 m